


PEX-Al-PEX x Female Solder Adapter - QHPAPA__F

Specification Sheet

Dimensional Data: Inches and [mm] are subject to manufacturing tolerances and change without notice.



Part	Nominal	'A'	'B'	'C'
Number	Size	in [mm]	in [mm]	in [mm]
QHPAPA22F	3/8" Pex-Al-Pex Comp. x 1/2" Female Solder	0.330 [8.4]	0.73 [18.6]	1.48 [37.5]
QHPAPA33F	1/2" Pex-Al-Pex Comp. x 1/2" Female Solder	0.482[12.2]	0.73 [18.6]	1.42 [36.0]
QHPAPA34F	1/2" Pex-Al-Pex Comp. x 3/4" Female Solder	0.482[12.2]	1.00 [25.5]	1.73 [44.0]
QHPAPAJ4F	5/8" Pex-Al-Pex Comp. x 3/4" Female Solder	0.620 [15.7]	1.00 [25.5]	1.72 [43.5]
QHPAPA44F	3/4" Pex-Al-Pex Comp. x 3/4" Female Solder	0.781 [19.8]	1.00 [25.5]	1.59 [40.3]
QHPAPA55F	1" Pex-Al-Pex Comp. x 1" Female Solder	0.998 [25.3]	1.28 [32.5]	1.75 [44.5]

Engineering Specification: ZurnPEX® brass PEX-AI-PEX	Accessories	
compression x female solder adapter. The QHPAPAF adapter	Q2PAPX	3/8" Alumicor® PEX-AI-PEX
to transition from copper pipe to PEX-AI-PEX tubing. Tubing is	Q3PAPX	1/2" Alumicor® PEX-AI-PEX
sealed with the use of two buna-N O-rings per barb. For use	QJPAPX	5/8" Alumicor® PEX-AI-PEX
with PEX-AI-PEX Alumicor® tubing made to ASTM F1281. For	Q4PAPX	3/4" Alumicor® PEX-AI-PEX
use in radiant heating and snow melting systems.	Q5PAPX	1" Alumicor® PEX-AI-PEX

Rev. A Date: 11/06/08 C.N. No. 99355 Dwg. No. 83670 Prod. No. QHPAPA_F